



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.




① ACB-XXAFFM-SL7000
Color: Black

② Cable

6P	PVC	6.5	20	ACB-06AFFM-SL7AXX
5P		6.0		ACB-05AFFM-SL7AXX
4P		5.5		ACB-04AFFM-SL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

6 Gray 灰	5 Green 綠	4 White 白
5 Yellow 黃	4 White 白	3 Black 黑
4 Green 綠	3 Black 黑	2 Blue 藍
3 White 白	2 Blue 藍	1 Brown 棕
2 Blue 藍	1 Brown 棕	
1 Brown 棕		
Pin # Wire	Pin # Wire	Pin # Wire
Pin Out		




Pin Assignments Front View

ACB-XXAFFM-SL7AXX

04: 4Pin
06: 6Pin

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
99 : 99Meters

Cable Length(L): 01~99Meters



Note:
* ⌀ Important Dimension To Check.
* Waterproof Rate: IP67
* Housing: Nylon+GF, Black.
* Female Pin: Copper Alloy, Gold Plated.
* Screw Nut: Nylon+GF, Black.
* Cable: UL2464 20AWG+D+Al/My
PVC Jacket UV Resistant, Black.
* Cable Length Tolerance: 01M: 40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE MIDDLE CABLE SCREW F CONN F PIN		
TOLERANCE	±0.5	SCALE 1:1	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV. A.1	QC: Inspection item		

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Jinhai	DATE 2015-07-16
DWG NO ACB-XXAFFM-SL7AXX	CHECKED BY Rensong	DATE 2015-07-16
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-07-16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACB-04AFFM-SL7A01](#) [ACB-04AFFM-SL7A03](#) [ACB-04AFMM-SL7A01](#) [ACB-06AFFM-SL7A01](#) [ACB-05AFFM-SL7A01](#) [ACB-05AFMM-SL7A01](#)