



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION




Conn.



1 ACB-XXAFMM-LL7000
Color: Black

2 Cable




5	Green 綠	4	White 白
4	White 白	3	Black 黑
3	Black 黑	2	Blue 藍
2	Blue 藍	1	Brown 棕
1	Brown 棕		

Pin # Wire


4	White 白
3	Black 黑
2	Blue 藍
1	Brown 棕

Pin # Wire

Pin Out



5 Pin



4 Pin

Pin Assignments Front View

ACB-XXAFMM-LL7AXX
04: 4Pin
05: 5Pin
XX : 01~99Meters
01 : 01Meter
02 : 02Meters
99 : 99Meters
Cable Length(L): 01~99Meters

- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Tin Plated.
 - * Lock Nut: Nylon+GF, Black.
 - * Cable: UL2464 20AWG+D+AI/My PVC Jacket UV Resistant, Black.
 - * Cable Length Tolerance: 01M: 40mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

5P	PVC	6.0	20	ACB-05AFMM-LL7AXX
4P		5.5		ACB-04AFMM-LL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

UNIT:mm
TOLERANCE ± 0.5

TITLE MIDDLE CABLE LOCK F CONN M PIN			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Jinhai	DATE 2015-07-17
DWG NO ACB-XXAFMM-LL7AXX	CHECKED BY Rensong	DATE 2015-07-17
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-07-17

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACB-04AFMM-LL7A02](#) [ACB-04AFMM-LL7A05](#) [ACB-04AFMM-LL7A10](#) [ACB-05AFMM-LL7A02](#) [ACB-05AFMM-LL7A05](#) [ACB-05AFMM-LL7A10](#) [ACB-05AFMM-LL7A03](#) [ACB-05AFMM-LL7A04](#)