



Conn.



1 ACB-XXAFMM-SL7000
Color: Black

2 Cable



5	Green	綠
4	White	白
3	Black	黑
2	Blue	藍
1	Brown	棕

Pin # Wire

4	White	白
3	Black	黑
2	Blue	藍
1	Brown	棕

Pin # Wire

Pin Out

ACB-XXAFMM-SL7AXX
04: 4Pin
05: 5Pin


XX : 01~99Meters
01 : 01Meter
02 : 02Meters

99 : 99Meters


Cable Length(L): 01~99Meters

Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Screw Nut: Nylon+GF, Black.
- * Cable: UL2464 20AWG+D+Al/My
- * PVC Jacket UV Resistant, Black.
- * Cable Length Tolerance: 01M: 40mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm



5 Pin



4 Pin

Pin Assignments Front View

5P	PVC	6.0	20	ACB-05AFMM-SL7AXX
4P		5.5		ACB-04AFMM-SL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

UNIT:mm
TOLERANCE ± 0.5

TITLE
MIDDLE
CABLE SCREW F CONN M PIN

SCALE 1:1	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV. A.1	$\varnothing$: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Jinhai	DATE 2015-07-17
DWG NO ACB-XXAFMM-SL7AXX	CHECKED BY Rensong	DATE 2015-07-17
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-07-17

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACB-04AFMM-SL7A02](#) [ACB-04AFMM-SL7A05](#) [ACB-04AFMM-SL7A10](#) [ACB-05AFMM-SL7A02](#) [ACB-05AFMM-SL7A05](#) [ACB-05AFMM-SL7A10](#)