



REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.



1 ACB-XXBFFM-LL7000  
Color: Black

6P	PVC	6.5	20	ACB-06BFFM-LL7AXX
5P		6.0		ACB-05BFFM-LL7AXX
4P		5.5		ACB-04BFFM-LL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

6 Gray 灰  
5 Yellow 黃  
4 Green 綠  
3 White 白  
2 Blue 藍  
1 Brown 棕

Pin # Wire


5 Green 綠  
4 White 白  
3 Black 黑  
2 Blue 藍  
1 Brown 棕

Pin # Wire


4 White 白  
3 Black 黑  
2 Blue 藍  
1 Brown 棕

Pin # Wire


Pin Out



6 Pin



5 Pin



4 Pin

Pin Assignments Front View

ACB-XXBFFM-LL7AXX

04: 4Pin

06: 6Pin


XX : 01~99Meters

01 : 01Meter

02 : 02Meters

99 : 99Meters


Cable Length(L): 01~99Meters



Note:

- \*  $\varnothing$  Important Dimension To Check
- \* Waterproof Rate: IP67
- \* Housing: Nylon+GF, Black
- \* Female Pin: Copper Alloy, Gold Plated
- \* Lock Nut: Nylon+GF, Black
- \* Cable: UL2464 20AWG+D+Al/My, PVC Jacket UV Resistant, Black
- \* Cable Length Tolerance: 01M:±40mm  
02M~05M:±60mm  
06M~10M:±100mm  
11M~30M:±200mm  
31M~99M:±500mm

UNIT:mm



TOLERANCE

±0.5 mm

TITLE

Middle  
Cable Lock F Conn F Pin

SCALE

1:1

SIZE

A4

SHEET

1

OF

1

REV.

A

WC-REV.

A.1

 $\varnothing$  Inspection item

# Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

ACB-XXBFFM-LL7AXX

CUSTOMER

ALTW

DRAWN BY

Vicky

CHECKED BY

Mafei

APPROVED BY

Max

DATE

2017-07-18

DATE

2017-07-18

DATE

2017-07-18

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACB-04BFFM-LL7A01](#) [ACB-05BFFM-LL7A01](#) [ACB-06BFFM-LL7A01](#) [ACB-04BFMM-LL7A01](#) [ACB-05BFMM-LL7A01](#)