



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.




1 ACB-XXBFFM-SL7000
Color: Black

2 Cable


Contacts	Cable Jacket	Cable OD	AWG	Item No.
6P	PVC	6.5	20	ACB-06BFFM-SL7AXX
5P		6.0		ACB-05BFFM-SL7AXX
4P		5.5		ACB-04BFFM-SL7AXX

6 Gray 灰	5 Green 綠	4 White 白
5 Yellow 黃	4 White 白	3 Black 黑
4 Green 綠	3 Black 黑	2 Blue 藍
3 White 白	2 Blue 藍	1 Brown 棕
2 Blue 藍	1 Brown 棕	
1 Brown 棕		
Pin # Wire	Pin # Wire	Pin # Wire
Pin Out		



Pin Assignments Front View

ACB-XXBFFM-SL7AXX
04: 4Pin
06: 6Pin
XX : 01~99Meters
01 : 01Meter
02 : 02Meters
99 : 99Meters
Cable Length(L): 01~99Meters



Note:
* Important Dimension To Check
* Waterproof Rate: IP67
* Housing: Nylon+GF, Black
* Female Pin: Copper Alloy, Gold Plated
* Screw Nut: Nylon+GF, Black
* Cable: UL2464 20AWG+D+Al/My, PVC Jacket UV Resistant, Black
* Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE Middle Cable Screw F Conn F Pin
TOLERANCE ±0.5 mm	SCALE 1:1	SIZE A4
	REV. A	WC-REV. A.1
		QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2017-07-18
DWG NO ACB-XXBFFM-SL7AXX	CHECKED BY Mafei	DATE 2017-07-18
CUSTOMER ALTW	APPROVED BY Max	DATE 2017-07-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACB-04BFFM-SL7A03](#)