





6P	PVC	6.5	20	ACB-06BFFM-SL7AXX
5P		6.0		ACB-05BFFM-SL7AXX
4P		5.5		ACB-04BFFM-SL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.


6	Gray	灰	5	Green	綠	4	White	白
5	Yellow	黃	4	White	白	3	Black	黑
4	Green	綠	3	Black	黑	2	Blue	藍
3	White	白	2	Blue	藍	1	Brown	棕
2	Blue	藍	1	Brown	棕			
1	Brown	棕						
Pin # Wire			Pin # Wire			Pin # Wire		
			Pin Out					



6 Pin




5 Pin




4 Pin

Pin Assignments Front View



ACB-XXBFFM-SL7000
Color: Black



Note :

- * Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Screw Nut: Nylon+GF, Black
- * Cable: UL2464 20AWG+D+Al/My,
PVC Jacket UV Resistant, Black
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

ACB-XXBFFM-SL7AXX


04:4Pin ———— ↑

:
:

06:6Pin

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

Cable Length(L):01~99Meters

UNIT:mm		TITLE Middle Cable Screw F Conn F Pin		
TOLERANCE ±0.5 mm		SCALE 1:1	SIZE A4	SHEET 1 OF 1
		REV. A	WC-REV. A.1	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2017-07-18
DWG NO ACB-XXBFFM-SL7AXX	CHECKED BY Mafei	DATE 2017-07-18
CUSTOMER ALTW	APPROVED BY Max	DATE 2017-07-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACB-04BFMM-SL7A01](#) [ACB-05BFMM-SL7A01](#) [ACB-04BFFM-SL7A01](#) [ACB-05BFFM-SL7A01](#) [ACB-06BFFM-SL7A01](#)