




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

	1	2	3	4	5	6	7	8																									
F																																	
E																																	
D	Ordering Information: ACBD-08BFFC-LL7XP0 Material Specification: * Connector: Nylon+GF, Black. * Pins: Copper Alloy, Gold Plated. * Seal & O-Ring: Silicone, Gray. * UL Rated: UL 94V-0, fl. * RoHS Compliant. Electrical Specification: * Contact Resistance: 10mΩ Max. * Insulation Resistance: 100MΩ Min. * Dielectric Withstand Voltage: 1,600 Vac. Mechanical Specification: * Durability: 1000 Cycles. * Tensile strength: 10 kgf. * Wire Conductor: 5A: 22AWG~20AWG 10A: 18AWG~16AWG * Wire Insulation OD: 5A: 1.9mm Max. 10A: 2.7mm Max. * Torque Force for Clamp Ring: 6~8 kgf-cm * Torque Force for Seal Nut: 6~8 kgf-cm Environmental Specification: * Waterproof Rating: IP67(Mated) * Temperature Range: -40°C to 105°C. * Salt Spray: Mated, 1000 Hours. * Safety Compliance: UL 1977. A: With Red&Yellow&Blue Color Seal S: With Red Color Seal, Cable OD 6.0~8.0mm. M: With Yellow Color Seal, Cable OD 8.0~10.0mm. L: With Blue Color Seal, Cable OD 10.0~12.0mm.																																
C																																	
B																																	
A	<table><tr><td>UNIT:mm</td><td></td><td colspan="2">TITLE Circular C-Size Field Installable Cable Type F Conn</td><td colspan="2" rowspan="3"> Amphenol LTW 安費諾亮泰企業股份有限公司 </td><td>ITEM NO</td><td>DRAWN BY Peng</td><td>DATE 2018-12-15</td></tr><tr><td colspan="2">TOLERANCE ±0.5 mm</td><td>SCALE 8:5</td><td>SIZE A4</td><td>SHEET 2 OF 2</td><td>DWG NO ACBD-08BFFC-LL7XP0</td><td>CHECKED BY Mafei</td><td>DATE 2018-12-15</td></tr><tr><td colspan="2"></td><td>REV. A</td><td>WC-REV. A.3</td><td>QC:Inspection item</td><td>CUSTOMER ALTW</td><td>APPROVED BY Jerry</td><td>DATE 2018-12-15</td></tr></table>								UNIT:mm	 	TITLE Circular C-Size Field Installable Cable Type F Conn		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO	DRAWN BY Peng	DATE 2018-12-15	TOLERANCE ±0.5 mm		SCALE 8:5	SIZE A4	SHEET 2 OF 2	DWG NO ACBD-08BFFC-LL7XP0	CHECKED BY Mafei	DATE 2018-12-15			REV. A	WC-REV. A.3	QC:Inspection item	CUSTOMER ALTW	APPROVED BY Jerry	DATE 2018-12-15
UNIT:mm	 	TITLE Circular C-Size Field Installable Cable Type F Conn		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO	DRAWN BY Peng	DATE 2018-12-15																									
TOLERANCE ±0.5 mm		SCALE 8:5	SIZE A4			SHEET 2 OF 2	DWG NO ACBD-08BFFC-LL7XP0	CHECKED BY Mafei	DATE 2018-12-15																								
		REV. A	WC-REV. A.3			QC:Inspection item	CUSTOMER ALTW	APPROVED BY Jerry	DATE 2018-12-15																								
	1	2	3	4	5	6	7	8																									

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACBD-08BFFC-LL7AP0](#)