



Conn.



Pin Assignments
Front View

3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		



① ACC-03AFFM-LL7000
Color: Black

② Cable

ACC-03AFFM-LL7A_{XX}

_{XX} : 01~99Meters
₀₁ : 01Meter
₀₂ : 02Meters


...

₉₉ : 99Meters

Cable Length(L): 01~99Meters

Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Lock Nut: Nylon+GF, Black.
- * Cable: UL2464 16AWG*3C+D+AI/My
PVC Jacket UV Resistant, OD=7.5, Black.
- * Cable Length Tolerance: 01M: 40mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm



UNIT:mm	
TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^\circ$

TITLE MIDDLE CABLE LOCK 3P F CONN F PIN			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.1	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Jinhai	DATE 2015-07-16
DWG NO ACC-03AFFM-LL7A _{XX}	CHECKED BY Rensong	DATE 2015-07-16
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-07-16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACC-03AFFM-LL7A02](#) [ACC-03AFFM-LL7A05](#) [ACC-03AFFM-LL7A03](#)