




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B		2019-03-06	Su Nan	Update Dimensional Tolerances



Conn.



Pin Assignments
Front View

3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		

ACC-03AFFM-SL7AXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
99 : 99Meters
Cable Length(L): 01~99Meters

Note:
* $\varnothing$ Important Dimension To Check.
* Waterproof Rate: IP67
* Housing: Nylon+GF, Black.
* Female Pin: Copper Alloy, Gold Plated.
* Screw Nut: Nylon+GF, Black.
* Cable: UL2464 16AWG*3C+D+Al/My
PVC Jacket UV Resistant, OD=7.5, Black.
* Cable Length Tolerance: 01M: 40mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT:mm		TITLE	
TOLERANCE		MIDDLE	
$\pm 0.5\text{mm}$ $\triangle B$		CABLE SCREW 3P F CONN F PIN	
SCALE	1:1	SIZE	A4
REV.	B	WC-REV.	B.1
		SHEET	1 OF 1
		$\varnothing$: Inspection item	

Amphenol LTW		ITEM NO	ACC-03AFFM-SL7AXX	DRAWN BY	Su Nan	DATE	2019-03-06
安費諾亮泰企業股份有限公司		DWG NO	ACC-03AFFM-SL7AXX	CHECKED BY	Peng	DATE	2019-03-06
		CUSTOMER	ALTW	APPROVED BY	Jerry	DATE	2019-03-06

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACC-03AFFM-SL7A01](#)