



Conn.



1 ACD-XXAFMM-LL7000
Color: Black



9P	PVC	6.0	24	ACD-09AFMM-LL7AXX
8P		5.5		ACD-08AFMM-LL7AXX
7P		5.8		ACD-07AFMM-LL7AXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.


9 Black 黑	8 Green 綠	7 Green 綠
8 Red 紅	7 Yellow 黃	6 White 白
7 Pink 粉紅	6 Orange 橙	5 Brown 棕
6 Gray 灰	5 Red 紅	4 Red 紅
5 Yellow 黃	4 Blue 藍	3 Yellow 黃
4 Green 綠	3 White 白	2 Orange 橙
3 White 白	2 Brown 棕	1 Blue 藍
2 Blue 藍	1 Black 黑	
1 Brown 棕		

Pin # Wire


Pin # Wire

Pin # Wire


Pin Out



9 Pin



8 Pin



7 Pin

Pin Assignments Front View

ACD-XXAFMM-LL7AXX

07: 7Pin

09: 9Pin

XX: 01~99Meters

01: 01Meter

02: 02Meters

XX: 99Meters

Cable Length(L): 01~99Meters

Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Lock Nut: Nylon+GF, Black
- * Cable: UL2464 24AWG+Drain+Al/My
- * PVC Jacket UV Resistant, Black.
- * Cable Length Tolerance: 01M: 40mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT:mm		TITLE MIDDLE CABLE LOCK F CONN M PIN		
TOLERANCE ± 0.5		SCALE 1:1	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV. A.1	$\varnothing$: Inspection item		

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Jinhai	DATE 2015-07-16
DWG NO ACD-XXAFMM-LL7AXX	CHECKED BY Rensong	DATE 2015-07-16
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-07-16

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACD-07AFMM-LL7A02](#) [ACD-07AFMM-LL7A05](#) [ACD-09AFMM-LL7A10](#) [ACD-07AFMM-LL7A10](#) [ACD-08AFMM-LL7A02](#) [ACD-08AFMM-LL7A05](#) [ACD-08AFMM-LL7A10](#) [ACD-09AFMM-LL7A02](#) [ACD-09AFMM-LL7A05](#)