



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.



1 ACD-XXBFMM-LL7000
Color: Black



Contacts	Cable Jacket	Cable OD	AWG	Item No.
9P	PVC	6.0	24	ACD-09BFMM-LL7AXX
8P		5.5		ACD-08BFMM-LL7AXX
7P		5.8		ACD-07BFMM-LL7AXX


9 Black 黑	8 Green 綠	7 Green 綠
8 Red 紅	7 Yellow 黃	6 White 白
7 Pink 粉紅	6 Orange 橙	5 Brown 棕
6 Gray 灰	5 Red 紅	4 Red 紅
5 Yellow 黃	4 Blue 藍	3 Yellow 黃
4 Green 綠	3 White 白	2 Orange 橙
3 White 白	2 Brown 棕	1 Blue 藍
2 Blue 藍	1 Black 黑	
1 Brown 棕		

Pin # Wire


Pin # Wire

Pin # Wire


Pin Out



9 Pin



8 Pin



7 Pin

Pin Assignments Front View

ACD-XXBFMM-LL7AXX
07: 7Pin
09: 9Pin
XX: 01~99Meters
01: 01Meter
02: 02Meters
XX: 99Meters
Cable Length(L): 01~99Meters

Note:
* Important Dimension To Check
* Waterproof Rate: IP67
* Housing: Nylon+GF, Black
* Male Pin: Copper Alloy, Gold Plated
* Lock Nut: Nylon+GF, Black
* Cable: UL2464 24AWG+Drain+Al/My, PVC Jacket UV Resistant, Black
* Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE
TOLERANCE	±0.5 mm	Middle Cable Lock F Conn M Pin
SCALE	1:1	SIZE A4
REV.	A	WC-REV. A.1
		QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
ACD-XXBFMM-LL7AXX	Vicky	2017-07-18
ALTW	Mafei	2017-07-18
	Max	2017-07-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ACD-07BFMM-LL7A01](#) [ACD-08BFMM-LL7A01](#) [ACD-09BFMM-LL7A01](#)