




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-040130	2010/04/14	Rex	Conn. Change
C	LE31110097-100	2011/01/20	Vicky	Mini Size Molding外觀變更
D	LEN1580057-060	2015/07/15	Vicky	Update Logo



Conn.



AD-02BMMM-LL7AXX
XX: 01~99Meters
01: 01Meter
02: 02Meters
:
:
:
99: 99Meters
Cable Length(L): 01~99Meters



Pin Assignments
Front View

2	Red	紅
1	Black	黑
Conn.	Wire Color	
Pin Out		

- Note:
- * $\varnothing$ Important Dimension
 - * Waterproof Rate: IP67
 - * Connector: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 24AWG*2C+D+A, Black, PVC Jacket, UV Resistant, OD=4.2mm
 - * Cable Length Tolerance: 01M: ± 40 mm
02M~05M: ± 100 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT:mm		TOLERANCE		TITLE		Amphenol LTW		ITEM NO		DRAWN BY		DATE	
± 0.5 mm				Mini, Cable Lock 2P M Conn M Pin		安費諾亮泰企業股份有限公司		AD-02BMMM-LL7AXX		Vicky		2015-07-15	
				SCALE 3:2						CHECKED BY Rita		DATE 2015-07-15	
				REV. D		WC-REV. A.3		CUSTOMER ALTW		APPROVED BY Lion		DATE 2015-07-15	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AD-02BMMM-LL7A02](#) [AD-02BMMM-LL7A10](#) [AD-02BMMM-LL7A05](#) [AD-02BMMM-LL7A01](#)