






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN-8A0135	2008/09/15	Shin	Add Notes
D	LEN1640066	2016/03/30	Vicky	Update Logo
E	CI90268	2019/02/18	Ruru	Modify Note




With Liquid Glue



Pin Assignments
Front View



Recommended Panel Cut-Out



Note: A

- * Important Dimension
- * Waterproof Rate: IP67, Unmated
- * Housing: Thermoplastic, Black
- * Pin: Copper Alloy, Gold Plated
- * Nut: Thermoplastic, Black
- * Gasket: Rubber, Black

- * Use with waterproof cap or dust cap
Panel thickness max: 2.5mm
- * Use without waterproof cap or dust cap
Panel thickness max: 3.5mm
- * Gasket and Nut are packed separately
in PE bags.

UNIT:mm		TITLE Mini Panel Lock 3Pin M Conn. M Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO AD-03PMMP-LS7001	DRAWN BY Ruru	DATE 2019-02-18
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 2:1	SIZE A4	SHEET 1 OF 1		DWG NO AD-03PMMP-LS7001	CHECKED BY Rita	DATE 2019-02-18
REV. E		WC-REV. A.2	QC: Inspection item			CUSTOMER ALTW	APPROVED BY Max	DATE 2019-02-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AD-03PMMP-LS7001](#)