

Conn.



ADC-XXAFM-SL7AXX

02: 2Pin ———— ↑

⋮

07: 7Pin

XX : 01~99Meters


01 : 01Meter

02 : 02Meters

⋮

99 : 99Meters

Cable Length(L): 01~99Meters



Note:


- \*  Important Dimension To Check.
- \* Waterproof Rate: IP67
- \* Housing: Nylon+GF, Black.
- \* Female Pin: Copper Alloy, Gold Plated.
- \* Cable: UL2464 16AWG+D+AL/My  
PVC Jacket UV Resistant, Black.
- \* Cable Length Tolerance: 01M:40mm  
02M~05M:±60mm  
06M~10M:±100mm  
11M~30M:±200mm  
31M~99M:±500mm

|           |                                                                                     |                                            |                |                     |
|-----------|-------------------------------------------------------------------------------------|--------------------------------------------|----------------|---------------------|
| UNIT : mm |  | TITLE<br>LARGE<br>CABLE SCREW F CONN F PIN |                |                     |
| TOLERANCE | ±0.5                                                                                | SCALE<br>1 : 1                             | SIZE<br>A4     | SHEET<br>1 OF 2     |
|           |                                                                                     | REV.<br>A                                  | WC-REV.<br>A.1 | QC: Inspection item |

Amphenol LTW  
安費諾亮泰企業股份有限公司

|                   |             |            |
|-------------------|-------------|------------|
| ITEM NO           | DRAWN BY    | DATE       |
|                   | Jinhai      | 2015-07-18 |
| DWG NO            | CHECKED BY  | DATE       |
| ADC-XXAFFM-SLTAXX | Rensong     | 2015-07-18 |
| CUSTOMER          | APPROVED BY | DATE       |
| ALTW              | Jerry       | 2015-07-18 |

| REV. | ECN NO. | DATE | SIGN | DESCRIPTION |
|------|---------|------|------|-------------|
|      |         |      |      |             |
|      |         |      |      |             |
|      |         |      |      |             |



7 Red 紅  
6 Gray 灰  
5 Yellow 黃  
4 Green 綠  
3 White 白  
2 Blue 藍  
1 Brown 棕

Pin # Wire

6 Gray 灰  
5 Yellow 黃  
4 Green 綠  
3 White 白  
2 Blue 藍  
1 Brown 棕

Pin # Wire

5 White 白  
4 Brown 棕  
3 Blue 藍  
2 Black 黑  
1 Red 紅

Pin # Wire

4 Orange 橙  
3 Red 紅  
2 Brown 棕  
1 Black 黑

Pin # Wire


3 Black 黑  
2 Blue 藍  
1 Brown 棕

Pin # Wire


2 Black 黑  
1 Red 紅

Pin # Wire


Pin Out




7 Pin




6 Pin




5 Pin



4 Pin




3 Pin



2 Pin

Pin Assignments Front View

UNIT:mm



TOLERANCE  
.X ±0.25  
.XX ±0.1  
.XXX ±0.05  
ANGLES ±1°

TITLE  
LARGE  
CABLE SCREW F CONN F PIN

SCALE 1:1 SIZE A4 SHEET 2 OF 2

REV. A WC-REV. A.1 QC:Inspection item

**Amphenol LTW**  
安費諾亮泰企業股份有限公司

ITEM NO  
DWG NO  
ADC-XXAFFM-SL7AXX  
CUSTOMER  
ALTW

DRAWN BY  
Jinhai  
CHECKED BY  
Rensong  
APPROVED BY  
Jerry

DATE  
2015-07-18  
DATE  
2015-07-18  
DATE  
2015-07-18

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[ADC-02AFFM-SL7A02](#) [ADC-02AFFM-SL7A05](#) [ADC-02AFFM-SL7A10](#) [ADC-03AFFM-SL7A02](#) [ADC-03AFFM-SL7A05](#) [ADC-07AFFM-SL7A10](#) [ADC-05AFFM-SL7A10](#) [ADC-06AFFM-SL7A02](#) [ADC-06AFFM-SL7A05](#) [ADC-06AFFM-SL7A10](#) [ADC-07AFFM-SL7A02](#) [ADC-07AFFM-SL7A05](#) [ADC-03AFFM-SL7A10](#) [ADC-04AFFM-SL7A02](#) [ADC-04AFFM-SL7A05](#) [ADC-04AFFM-SL7A10](#) [ADC-05AFFM-SL7A02](#) [ADC-05AFFM-SL7A05](#)