




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1590474	2015/08/18	Jinhai	Change Pin Out
C	C191527	2019-08-21	Fu	Modify the Title



18	Blue/White	藍/白
17	Green/White	綠/白
16	Orange/White	橙/白
15	Red/White	紅/白
14	Brown/White	棕/白
13	Black/White	黑/白
12	Light Green	淺綠
11	Purple	紫
10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		



Pin Assignments

Front View

ADD-18AFFM-LL7AXX

```


XX : 01~99Meters
01 : 01Meter
02 : 02Meters
.
.
.
99 : 99Meters

```

Cable Length(L):01~99Meters

Note :

- * **Important Dimension To Check.**
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Lock Nut: Nylon+GF, Black.
- * Cable: UL2464 24AWG*18C+D+AL/My
PVC Jacket UV Resistant, OD=8.0, Black.
- * Cable Length Tolerance: 01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



UNIT: mm		TITLE	LARGE	
TOLERANCE	± 0.5	SCALE	1:1	CABLE LOCK 18PIN F CONN F PIN
		SIZE	A4	SHEET 1 OF 1
		REV. C	WC-REV. A.1	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY FU	DATE 2019-08-21
DWG NO ADD-18AFFM-LL7AXX	CHECKED BY Feng li	DATE 2019-08-21
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2019-08-21

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ADD-18AFFM-LL7A02](#) [ADD-18AFFM-LL7A10](#) [ADD-18AFFM-LL7A06](#)