


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1590477	2015/08/18	Jinhai	Change Pin Out



ALTW
CONFIDENTIAL
2015-08-18
R&D DEPT.

ALTW
DCC. DEPT.
CONFIDENTIAL
2015.09.25
ISSUED

18	Blue/White	藍/白
17	Green/White	綠/白
16	Orange/White	橙/白
15	Red/White	紅/白
14	Brown/White	棕/白
13	Black/White	黑/白
12	Light Green	淺綠
11	Purple	紫
10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
Pin Out		


ADD-18AFMM-SL7000
Color: Black

ADD-18AFMM-SL7AXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

Cable Length(L): 01~99Meters

- Note:
- * Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon+GF, Black.
 - * Cable: UL2464 24AWG*18C+D+AL/My
PVC Jacket UV Resistant, OD=8.0, Black.
 - * Cable Length Tolerance: 01M: 40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm



Pin Assignments
Front View

UNIT:mm		TITLE	LARGE CABLE SCREW 18PIN F CONN M PIN		
TOLERANCE		SCALE	1:1	SIZE	A4
±0.5		REV.	B	WC-REV.	A.1
		SHEET 1 OF 1			
		QC: Inspection item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Jinhai	2015-08-18
ADD-18AFMM-SL7AXX	CHECKED BY	DATE
	Rensong	2015-08-18
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2015-08-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ADD-18AFMM-SL7A02](#) [ADD-18AFMM-SL7A05](#) [ADD-18AFMM-SL7A10](#)