



REFERENCE DIMENSIONS - ASSEMBLED



KIT CONTENTS

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A	-	RELEASE	10/SEP/13	DRP	

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

HOUSING: THERMOPLASTIC; COLOR: GREY
WEDGELOCK: THERMOPLASTIC; COLOR: ORANGE
SEALS: SILICONE RUBBER
CONTACTS: COPPER ALLOY; NICKEL PLATED

2. SPECIFICATIONS:

- 2.1 CURRENT RATING: 25 AMPS
- 2.2 OPERATING TEMPERATURE: -55°C TO +125°C
- 2.3 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
- 2.4 INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 25°C.
- 2.5 CONTACT MILLIVOLT DROP: 60 MILLIVOLT DROP @ 25 AMP TEST CURRENT.
- 2.6 MOISTURE RESISTANCE: IP67 (MATED CONDITION)
- 2.7 CONNECTOR MATING CYCLE DURABILITY: 100 CYCLES

3. MATING PART: ATP06-4S* PLUG
(* = MODIFICATIONS AND COLORS)

4. AVAILABLE HAND CRIMPER: CA-5D12

5. ALL COMPONENTS ARE RoHS COMPLIANT.

6. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

7 WIRE RANGE OF CONTACTS INCLUDED
IN KIT: 12 - 14 AWG


8 CONTACT SIZE AND REAR SEAL WIRE RANGE:

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	TYPICAL WIRE RANGE
12	3.40 mm (.134 in)	4.95 mm (.195 in)	10 - 14 AWG



4	AT60-204-12141	CONTACT, PIN, SOLID, SIZE 12, 12 - 14 AWG	3
1	AWP-4P	P-WEDGELOCK, 4 POSITION, ATP SERIES	2
1	ATP04-4P	RECEPTACLE, 4 POSITION, ATP SERIES	1
QUANTITY	PART NUMBER	DESCRIPTION	ITEM

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE		<h1>Amphenol</h1> <div>Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036</div>																		
1) All dimensions are in metric(mm).		DRAWN: D.PARKS		10/SEP/13																				
2) Tolerances are as follows:		CHECKED:																						
1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08		ENGINEER:																						
3) Note reference = 		APPROVAL:				<div>KIT, ATP SERIES, 4 POSITION, RECEPTACLE, CONTACTS, AND WEDGELOCK</div> <table><tr><td>SIZE</td><td>TYPE</td><td>DWG NO:</td><td colspan="2">REVISION</td></tr><tr><td>B</td><td>C-</td><td>ATP04-4P-KIT01</td><td colspan="2">A</td></tr><tr><td colspan="2">SCALE: NONE</td><td colspan="3">SHEET 1 OF 1</td></tr></table>				SIZE	TYPE	DWG NO:	REVISION		B	C-	ATP04-4P-KIT01	A		SCALE: NONE		SHEET 1 OF 1		
SIZE	TYPE	DWG NO:	REVISION																					
B	C-	ATP04-4P-KIT01	A																					
SCALE: NONE		SHEET 1 OF 1																						
MATERIAL SPECIFICATIONS:		CUSTOMER:																						
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.																						
NEXT ASSY:																								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ATP04-4P-KIT01](#)