




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8A0138~141	2008/09/10	Shin	Add Notes
C	LEN15B0222~225	2015/11/02	Ruru	Change Logo & Note



AU-04PMMM-LL7000
Color: Black

AU-04PMMM-LL7AXX
XX:01~99Meters
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

- Note:
- * @@Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 26AWG*4C+Drain+Al/My, PVC Jacket UV Resistant OD=4.8mm, Black
 - * Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
 - * Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
 - * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm



4	White	白
3	Green	綠
2	Red	紅
1	Brown	棕
Conn.	Wire Color	

UNIT:mm		TOLERANCE		TITLE		Mini Cable Lock 4Pin M Conn. M Pin		SCALE		SHEET 1 OF 1		REV. C		SIZE A4		QC :Inspection Item		Amphenol LTW		安費諾亮泰企業股份有限公司		ITEM NO		DWG NO		CUSTOMER		DRAWN BY		CHECKED BY		APPROVED BY		DATE		DATE		DATE	
±0.5 mm																								AU-04PMMM-LL7AXX		ALTW		Ruru		Rita		Lisa		2015/11/02		2015/11/02		2015/11/02	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AU-04PMMM-LL7A01](#) [AU-04PMMM-LL7A02](#) [AU-04PMMM-LL7A05](#) [AU-04PMMM-LL7A10](#)