




5		6		7		8	
REV.	ECN NO.	DATE	SIGN	DESCRIPTION			
B	LEN-910044~7	2008/12/26	TOMMY	ADD Dimension & NOTE			
C	LEN-0C0293~5	2010/10/16	Li Xiu Zhi	Change View			
D	LEN15C0358~61	2015/12/08	Ruru	Change Logo			

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



AU-05AFFM-SL6AXX

XX:01~99Meters

01:01 Meter


02:02Meters

:

:

99:99Meters

Cable Length(L):01~99Meters



Pin Assignments

Front View 前視圖

Yellow	黃	5
White	白	4
Red	紅	3
Brown	棕	2
Green	綠	1
Wire Color		Conn.
Out Pin		

Note:

- * @@Important Dimension To Check.
- * Waterproof Rate: IP66
- * Connector: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 26#*5C+Drain+Al.My
PVC Jacket UV Resistant OD=4.8mm, Black
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE		Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO	DRAWN BY	DATE
TOLERANCE ±0.5		Mini Cable Screw 5P F Conn F Pin			DWG NO	CHECKED BY	DATE
		SCALE	SHEET		AU-05AFFM-SL6AXX	Rita	2015/12/08
		REV.	SIZE	QC :Inspection Item	CUSTOMER	APPROVED BY	DATE
		D	A4		ALTW	Lisa	2015/12/08

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AU-05AFFM-SL6A10](#) [AU-05AFFM-SL6A02](#) [AU-05AFFM-SL6A05](#) [AU-05AFFM-SL6A01](#)