





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
D	LE31110076~079	2011/01/19	Vicky	Mini Size Molding外觀變更
E	LEN1150124~127	2011/05/19	Vicky	Modify Connector View.
F	LEN15C0383~386	2015/12/08	Ruru	Change Logo




AU-06BFFM-SL7AXX

- XX:01~99Meters
- 01:01Meter
- 02:02Meters
- :
- :
- 99:99Meters

Cable Length(L):01~99Meters

- Note:
- * @@Important Dimension.
 - * Waterproof Rate: IP67.
 - * Connector: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon+GF, Black.
 - * O-Ring: EPDM, Black.
 - * Cable:UL2464 26AWG*6C+D+A, PVC Jacket, UV Resistant, OD=5.0mm, Black
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
 Pin Out		

UNIT:mm	TITLE Mini,Cable Screw 6P F Conn F Pin	
TOLERANCE ±0.5 mm	SCALE Free	SHEET 1 OF 1
REV. F	SIZE A4	QC :Inspection Item

Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO	DRAWN BY Ruru	DATE 2015/12/08
		DWG NO AU-06BFFM-SL7AXX	CHECKED BY Rtia	DATE 2015/12/08
		CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015/12/08

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AU-06BFFM-SL7A05](#) [AU-06BFFM-SL7A02](#) [AU-06BFFM-SL7A01](#) [AU-06BFFM-SL7A10](#)