



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8A0116~119	2008/09/10	Shin	Add Notes
C	LEN-910025~028	2009/01/05	Ivan Lin	Update panel thickness
D	LEN15B0248~51	2015/11/03	Ruru	Change Logo & Tolerance



White	白	6
Red	紅	5
Orange	橙	4
Yellow	黃	3
Green	綠	2
Blue	藍	1
Wire Color	Conn.	
Out Pin		




AU-06PMMM-SL7000
Color: Black


AU-06PMMM-SL7AXX

XX: 01~99Meters
01: 01Meter
02: 02Meters
:
:
99: 99Meters

Cable Length(L): 01~99Meters



Pin Assignments
Front View



Recommended Panel Cut-Out

Note:

- * QC Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 26AWG*6C+Drain+Al/My Black, PVC Jacket UV Resistant OD=5.0mm
- C/B* Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- C/B* Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- C* Cable Length Tolerance: 01M: 40mm
02M~05M: 60mm
06M~10M: 100mm
11M~30M: 200mm
31M~99M: 500mm

UNIT:mm		
TOLERANCE	$\pm 0.5mm$ <u>C</u>	

TITLE Mini Cable Screw 6P M Conn M Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. D	WC-REV. A.1	<u>QC</u> : Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO AU-06PMMM-SL7AXX	DRAWN BY Ruru	DATE 2015-11-03
DWG NO AU-06PMMM-SL7AXX	CHECKED BY Rita	DATE 2015-11-03
CUSTOMER ALTW	APPROVED BY Lisa	DATE 2015-11-03

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AU-06PMMM-SL7A01](#) [AU-06PMMM-SL7A02](#) [AU-06PMMM-SL7A05](#) [AU-06PMMM-SL7A10](#)