



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016/05/12	Kaven	Change Rev.01 To Rev.A




Unmated Waterproof Rating: IPx8
(Under Water 1M 24hours)

RF5X-XXA1XXX-MHF801			
Contact Gender		Cable Type	Length:
(B) : F	Conn F Pin	(29) : RG178	(010) : 100mm
(C) : F	Conn M Pin	(53) : 1.13mm	(015) : 150mm
		(54) : 1.32mm	(020) : 200mm
		(55) : 1.37mm	(025) : 250mm
			(030) : 300mm




Note:

- * $\varnothing$ Important Dimension To Check.
- * Electrical:
- * Impedance: 50 Ω
- * V.S.W.R
- 0-3GHz : 1.3(Max) For RG178
- 0-3GHz : 1.3(Max) , 4-6GHz : 1.5(Max) For 1.13mm/1.32mm/1.37mm Cable
- * Conn 1: SMA Bulkhead Female, Gold Plated
- * Conn 2: MHF Male, Gold Plated
- * Temperature Range: -40 $^{\circ}$ C ~ 90 $^{\circ}$ C (It's subject to ALTW testing condition.)
- * Cable Length Tolerance : 100mm~150mm $\pm$ 10mm
160mm~300mm $\pm$ 15mm



Recommended
Panel Cut-Out



UNIT:mm				TITLE SMA Bulkhead Jack To MHF Male Cable Assembly			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Kaven		DATE 2016/05/12				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°									SCALE 2:1		SIZE A4		SHEET 1 OF 1		DWG NO RF5X-XXA1XXX-MHF801		CHECKED BY Doreen
				REV. A		WC-REV. A.1			QC: Inspection item		CUSTOMER ALTW		APPROVED BY Lisa		DATE 2016/05/12		

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RF5B-53A1030-MHF801](#) [RF5C-53A1030-MHF801](#)