




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Drain Wire	接地線	Shield
Brown	棕	8
White/Brown	白/棕	7
Green	綠	6
White/Blue	白/藍	5
Blue	藍	4
White/Green	白/綠	3
Orange	橘	2
White/Orange	白/橘	1
Wire Color		Plug
Pin Out		

Twist
Twist
Twist

RCP-5SBMMM-SLM7BXX
T
XX: 01~99Meters
01: 01Meters
02: 02Meters
99: 99Meters
Cable Length(L):01~99Meters

Note:
* Ⓞ Important Dimension
* Waterproof Rate: IP67
* Plug: 8P8C, Gold Plated, Shielded
* Screw Nut: Nylon+GF, Black
* Cable: CAT5E FTP 24#*4P+D
+Al/My(UV Resistant) OD=6.5mm, Black.
* Cable Length Tolerance: 01M: ±40mm
02~05M: ±60mm
06~10M: ±100mm
11~30M: ±200mm
30~99M: ±500mm

UNIT:mm		TITLE RJ45, C Size	Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO RCP-5SBMMM-SLM7BXX	DRAWN BY Tom	DATE 2014-08-29
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 1:1	SIZE A4	SHEET 1 OF 1	CUSTOMER ALTW	CHECKED BY Jerry	DATE 2014-08-29
		REV. A	WC-REV. A.2	QC: Inspection item		APPROVED BY Victor	DATE 2014-08-29

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RCP-5SBMMM-SLM7B01](#)