


A	UNIT:mm			TITLE			Amphenol LTW			ITEM NO		DRAWN BY		DATE		
	TOLERANCE			SCALE						SIZE		SHEET		CHECKED BY		DATE
	±0.5 mm			1:2			A4		1		OF		Rita		2018-12-05	
				REV. A			WC-REV. A.1		QC		Inspection item		APPROVED BY		DATE	
										CUSTOMER		Max		2018-12-05		
										ALTW						

4P	PVC	4.8	22	MI2D04ML-I2DFR-SDXXX
4P	PUR	4.0		MI2D04ML-I2DFR-SBXXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

M I2D XX M L - I2D F R - S X XXX

I2D: D-Code

04: 4Pin

XXX: 0.5~99Meters
A05: 0.5 Meter
001: 1 Meter
002: 2 Meters
:
099: 99 Meters

B: PUR UL20549 Cable,Black(PUR黑色外被線材)
D: PVC UL2517 Cable,Black(PVC黑色外被線材)

S: Screw(螺紋式)



R: Right(90°線端)

F: Female Connector(母座)

I2D: D-Code

M: Male Connector(公座)

L: Straight(180°線端)

Pin Out	5	--	
	4	Black	黑
	3	Blue	藍
	2	White	白
	1	Brown	棕
	Pin #	Wire	
C2			
	4P		
C1			
	4P		
Pin Assignments Front View			

UNIT:mm

TOLERANCE

TITLE MI2 D-Code Double Ended			
SCALE 1:2	SIZE A4	SHEET 2 OF 2	
REV. A	WC-REV. A.1	QC: Inspection item	

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2018-12-05
DWG NO MI2DXXML-I2DFR-SXXXX	CHECKED BY Rita	DATE 2018-12-05
CUSTOMER ALTW	APPROVED BY Max	DATE 2018-12-05

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M12D04ML-12DFR-SDA05](#) [M12D04ML-12DFR-SBA05](#)