



A	B	C	D	E	F
---	---	---	---	---	---

**F**

**E**

**D**

**C**

**B**

**A**

M SAP XX F R - SAP F R - S X XXX

SAP: A-Code Plastic Nut

03: 3Pin  
04: 4Pin  
05: 5Pin  
06: 6Pin  
08: 8Pin  
10: 10Pin  
12: 12Pin

F: Female Connector(母座)

R: Right(90°線端)

XXX: 0.5~99Meter  
A05: 0.5 Meter  
1: 01 Meter  
2: 02 Meters  
:  
99: 99 Meters

B: PUR UL20549 C  
D: PVC UL2517 Co

S: Screw(螺紋式)

R: Right(90°線端)

F: Female Connect

SAP: A-Code Plas

UNIT:mm		TITLE	MI2 A-Code Double Ended		
TOLERANCE		SCALE	1:2	SIZE	A4
± 0.5 mm		SHEET	2	OF	3
		REV.	A	QC-REV.	(QC): Inspection item

**Amphenol LTV**

**安費諾亮泰企業股份有限公司**

A	B	C	D	E	F
---	---	---	---	---	---

A	B	C	D	E	F
---	---	---	---	---	---

A	UNIT:mm			TITLE			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY		DATE			
	TOLERANCE  ± 0.5 mm			SCALE					SIZE		SHEET		CHECKED BY		DATE	
				1:2					A4		3 OF 3		Rita		2018-12-05	
				REV.					WC-REV.		QC: Inspection item		CUSTOMER		APPROVED BY	
				A					ALTW		Max		2018-12-05			
1		2		3		4		5		6		7		8		

W10814-03-0001A2

AUTHORIZED BY Amphenol LTW

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MSAP04FR-SAPFR-SDA05](#) [MSAP05FR-SAPFR-SDA05](#) [MSAP05FR-SAPFR-SBA05](#) [MSAP04FR-SAPFR-SBA05](#)  
[MSAP08FR-SAPFR-SDA05](#) [MSAP08FR-SAPFR-SBA05](#)