




	1	2	3	4	5	6
F	<div style="display: flex; justify-content: space-between; align-items: center;"> <div> <p>1.5</p> <p>QC L (mm)</p> </div> <div> <p>5.1</p> </div> </div>					






- \*  Important Dimension.
- \* Waterproof Rate: IP68, IP69K.
- \* Connector: PU+GF, Black.
- \* Pin: Copper Alloy, Gold Plated.
- \* Screw Nut: Nylon, Black.
- \* Outer Mold: PU, Black.
- \* Cable: (B) UL20549, PUR Jacket, Black.  
(D) UL2517, PVC Jacket, Black.
- \* Rated Voltage: 4Pin 250V dc. or ac.
- \* Rated Current: 4Pin 4A
- \* Cable Length Tolerance: 0.5±20mm  
01±40mm  
02M~05M:±60mm  
06M~10M:±100mm  
11M~30M:±200mm  
31M~99M:±500mm

UNIT:mm				TITLE MI2 D-Code Double Ended				Amphenol LTW  安費諾亮泰企業股份有限公司				ITEM NO		DRAWN BY Vicky		DATE 2018-12-12							
TOLERANCE  ±0.5 mm												SCALE 1:1		SIZE A4		SHEET 1 OF 2		DWG NO MSDPXXFR-SDPFR-SXXXX		CHECKED BY Rita		DATE 2018-12-12	
												REV. A		WC-REV. A.5		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Max		DATE 2018-12-12	
1		2		3		4		5		6		7		8		WI0814-03-BW01A							

A



Pin Out	5 -- 4 Black 黑 3 Blue 藍 2 White 白 1 Brown 棕
	Pin # Wire
C1 & C2	 4P
Pin Assignments Front View	

UNIT : mm				TITLE					
TOLERANCE				M12 D-Code Double Ended					
				SCALE 1 : 1		SIZE A4		SHEET 2 OF 2	
				REV. A		WC-REV. A.5		QC : Inspection item	

Amphenol LTW  
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Vicky	2018-12-12
DWG NO	CHECKED BY	DATE
MSDPXXFR-SDPFR-SXXXX	Rita	2018-12-12
CUSTOMER	APPROVED BY	DATE
ALTW	Max	2018-12-12

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MSDP04FR-SDPFR-SBA05](#) [MSDP04FR-SDPFR-SD001](#) [MSDP04FR-SDPFR-SDA05](#) [MSDP04FR-SDPFR-SB001](#)