




UNIT:mm				TITLE M12 D-Code Double Ended				Amphenol LTW 安費諾亮泰企業股份有限公司				ITEM NO		DRAWN BY Vicky		DATE 2018-12-12			
TOLERANCE ±0.5 mm				SCALE 1:2		SIZE A4						SHEET 1 OF 2		DWG NO MSDPXXML-SDPFL-SXXXX		CHECKED BY Rita		DATE 2018-12-12	
				REV. A		WC-REV. A.5						QC: Inspection item		CUSTOMER ALTW		APPROVED BY Max		DATE 2018-12-12	
1		2		3		4		5		6		7		8		WI0814-03-0001A			

4P	PVC	4.8	22	MSDP04ML-SDPFL-SDXXX
4P	PUR	4.0		MSDP04ML-SDPFL-SBXXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.

M SDP XX M L - SDP F L - S X XXX

SDP: D-Code Plastic Nut

04: 4Pin

XXX: 0.5~99Meters
A05: 0.5 Meter
001: 1 Meter
002: 2 Meters
:
099: 99 Meters

B: PUR UL20549 Cable,Black(PUR黑色外被線材)
D: PVC UL2517 Cable,Black(PVC黑色外被線材)

S: Screw(螺紋式)



L: Straight(180°線端)


F: Female Connector(母座)

SDP: D-Code Plastic Nut

M: Male Connector(公座)

L: Straight(180°線端)

Pin Out	5 -- 4 Black 黑 3 Blue 藍 2 White 白 1 Brown 棕
Pin #	Wire
C2	 4P
C1	 4P
Pin Assignments Front View	

UNIT:mm		TITLE M12 D-Code Double Ended	
TOLERANCE		SCALE 1:2	SIZE A4
		REV. A	WC-REV. A.5
		SHEET 2	OF 2
		QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Vicky	DATE 2018-12-12
DWG NO MSDPXXML-SDPFL-SXXXX	CHECKED BY Rita	DATE 2018-12-12
CUSTOMER ALTW	APPROVED BY Max	DATE 2018-12-12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MSDP04ML-SDPFL-SDA05](#) [MSDP04ML-SDPFL-SBA05](#) [MSDP04ML-SDPFL-SB001](#) [MSDP04ML-SDPFL-SD001](#)