




REV.	DESCRIPTION

- Notes:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP68, IP69K
 - * Connector: PU+GF, Black.
 - * Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon, Black
 - * Outer Mold: PU, Black.
 - * Cable: (B) UL20549, PUR Jacket, Black.
(D) UL2517, PVC Jacket, Black.
 - * Rated Voltage: 4Pin 250V dc. or ac.
 - * Rated Current: 4Pin 4A
 - * Cable Length Tolerance: 0.5±20mm
01±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm				TITLE MI2 D-Code Double Ended			Amphenol LTW 安費諾亮泰企業股份有限公司			ITEM NO		DRAWN BY Ruru		DATE 2018-12-12				
TOLERANCE ± 0.5 mm				SCALE 1:1		SIZE A4				SHEET 1 OF 2		DWG NO MSDPXXMR-SDPFR-SXXXX		CHECKED BY Rita		DATE 2018-12-12		
				REV. A		WC-REV. A.5				QC: Inspection item		CUSTOMER ALTW		APPROVED BY Max		DATE 2018-12-12		
1		2		3		4				5		6		7		8 W10814-03-BW01A2		

					6		7		8	
					4P		PVC		4.8	
					4P		PUR		4.0	
					Contacts		Cable Jacket		Cable OD	
							22		MSDP04MR-SDPFR-SDXXX	
							AWG		MSDP04MR-SDPFR-SBXXX	
									Item No.	

1

2

3

4

5

6

7

8

WI0814-03-0001A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MSDP04MR-SDPFR-SDA05](#) [MSDP04MR-SDPFR-SBA05](#) [MSDP04MR-SDPFR-SB001](#) [MSDP04MR-SDPFR-SD001](#)