

C504F Scalable Clip 1.0 mm

Part No. C504 10M006 118 3

- All-purpose (e.g. antenna or grounding contact)
- For flat contact area
- Same Pad-Layout for all scalable Clips
- SMT solderable
- Tape & Reel packaging
- Pick & Place capable



View represents all available contact positions.

For more information, please contact us [here](#).

Series Mobile Connectors
Subseries Mobile Connectors C504F

COMMON CHARACTERISTICS		
No. of contacts		1
Termination		solder
Total height (undeflected)		1.0 mm
Stroke		0.4 mm
CLIMATICAL CHARACTERISTICS		
Operating temperature		-40 °C...+85 °C
MECHANICAL CHARACTERISTICS		
Mechanical lifetime		100 mating cycles
Contact force		Min. 0.2 N
MATERIALS		
Contacts		Stainless steel
Plating contacts		min. 0.5 µm Au
Plating solder area		min. 0.025 µm Au
Underlayer		min. 1,27 µm Ni.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C504 10M006 118 3](#) [C707 10M008 669 2](#)