





MINIMSD



BUSSMANN PART TYPE(巴斯曼熔断器型号) :
1.MINI-MSDM000(WITHOUT FUSE) 2.MINI-MSDM080(FUSE=80A)
3.MINI-MSDMI00(FUSE=100A) 4.MINI-MSDMI25(FUSE=125A)
5.MINI-MSDMI60(FUSE=160A) 6.MINI-MSDM200(FUSE=200A)
7.MINI-MSDM250(FUSE=250A) 8.MINI-MSDM315(FUSE=315A)
9.MINI-MSDM350(FUSE=350A) 10.MINI-MSDM400(FUSE=400A)


ZHONGRONG PART TYPE(中熔熔断器型号) : B
1.MINI-MSDM080I(FUSE=80A) 2.MINI-MSDMI00I(FUSE=100A)
3.MINI-MSDMI25I(FUSE=125A) 4.MINI-MSDMI60I(FUSE=160A)
5.MINI-MSDM200I(FUSE=200A) 6.MINI-MSDM250I(FUSE=250A)
7.MINI-MSDM315I(FUSE=315A) 8.MINI-MSDM350I(FUSE=350A)
9.MINI-MSDM400I(FUSE=400A)

MINIMSD




MINI-MSD PLUG

FUSE 熔断器规格	80A	100A	125A	160A	200A	250A	315A	350A	400A	SHUNT
MARKING 对应插座印字	80A	100A	125A	160A	200A	250A	315A	350A	400A	SHUNT








LEVER IN LOCKED POSITON
锁紧后手柄位置




LEVER IN OPEND POSITON
打开后手柄位置

MINIMSD

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd Shenzhen		TITLE MINI-MSD SPEC MINI-MSDM-XXXX				
ANSI Y14.5M UNITS: MM Pro/E FILE	.X ±0.5 .XX ±0.30 ANGLES ±1.0°		ENGR JACK.D Apr-15-15						
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN	CHKD	SIZE A3	DWG NO. MINIMSD			REV B		
		APPD	CODE: 58982		SCALE:	SHEET 1 OF 2			



- NOTES:

DIMENSIONS ANSI Y14.5M UNITS: MM Pro/E FILE	TOLERANCES .X ±0.5 .XX ±0.30 ANGLES ±1.0°	PROJECTION 	Amphenol Pcd Shenzhen		TITLE MINI-MSDF-XXXX			
			ENGR JACK.D Apr-16-15					
ORIGINAL	<i>THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN</i>		CHKD		SIZE A3	DWG NO. MINIMSD		REV B
			APPD		CODE: 58982 SCALE:		SHEET 2 OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[MINIMSDF000F](#) [MINIMSDF000R](#) [C220006502](#) [L17D3D475T75](#)