



REV	SIGN	DATE	DESCRIPTION	APPROVER
B		2018-01-02	The first release	Zhishua
RoHS Compliant				
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Material:

- Item ① Contact pin: Copper, Tin plated
- Item ② Insulator(housing): Thermoplastic (UL94V-0)
- Item ③ With flange nut: Brass ,M2.5

Electrical: cULus

- Voltage rating: 300V
- Current rating: 20A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 
- Critical dimension: 

Fill the glue
SECTION K-K

OQ xx 5 5 x A xxxx G

No. OF POLES
02: 2 POLES
.....
24: 24 POLES

COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
White(RAL1102)
Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000 "®" Logo
000A "ANY" Logo
...
Any special item by
customer request,
please contact sales
department

SECTION P-P

DIMENSION

Dim A	(N+2) × 5.08
Dim B	(N-1) × 5.08
Dim C	(N-1) × 5.08+10.16
Dim D	(N-1) × 5.08+5.48

N = Number of poles

2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35
17p-24p	±0.40



RECOMMENDED P.C.B LAYOUT



Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE				OQ 5.08mm 90° /With Flange Series 特殊零件 (反向)				PROPERTY OF ANITEK TECHNOLOGY CO., LTD			
PART NO.				DWG NO.				80Q07439			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.						
		Zhihua 2018.01.02	Zhihua 2018.01.02			UNIT: mm		X. ±0.50			
						SCALE: NONE		X.X ±0.30			
						SHEET: 01/01		X.XX ±0.10			
						REV: B		X° ±1°			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[OQ05555A000AG](#)