



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-880086~089	2008/03/06	Gao Ling	Add Cross
C	LE314C0290~293	2014/12/08	Feng_Li	Change Pin Out
D	LEN1730037~040	2017/02/22	Ruru	Change Outer Mold Design




Conn. 1 & 2
Pin Assignments
Front View



PS-030300-FF0-TSAXX

XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters
Cable Length(L): 01~99meters



- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP68
一米水深, 24H
 - * Housing: Black, PU
 - * Female Pin: Copper Alloy, Gold Plated
 - * Wire Harness: UL1007, 24AWG, 3Pcs
 - * Cable: Black, UL2464 22AWG*3C+Talc
PVC Jacket(UV Resistant), OD=5.0mm
 - * Cable Length Tolerance: 01M: ± 40 mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

4	Black	黑	4
3	Blue	藍	3
1	Brown	棕	1
Conn. 1	Wire Color		Conn. 2
Pin Out			

UNIT:mm
TOLERANCE
比例 3:1
 ± 0.5 mm

TITLE M12 Conn T Cable Screw FF Conn FF Pin			
SCALE 1:1	SIZE A4	SHEET 1	OF 1
REV. D	WC-REV. A.2	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO PS-030300-FF0-TSAXX	DRAWN BY Ruru	DATE 2017-02-22
CUSTOMER ALTW	CHECKED BY Rita	DATE 2017-02-22
	APPROVED BY Max	DATE 2017-02-22

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PS-030300-FF0-TSA01](#) [PS-030300-FF0-TSA10](#) [PS-030300-FF0-TSA02](#) [PS-030300-FF0-TSA05](#)