




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-880354-357	2008/03/08	Li Chi Cheng	Add Cross
C	LE314C0294-297	2014/12/12	Feng_Li	Change Pin Out
D	LEN1730041-044	2017/02/22	Ruru	Change Outer Mold Design



Conn.1
Pin Assignments
Front View



Conn.2
Pin Assignments
Front View



PS-030300-MF0-TSAXX

XX: 01-99Meters
01: 01Meter
02: 02Meters
...
99: 99Meters
Cable Length(L): 01~99meters

- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP68
一米水深, 24H
 - * Housing: Black, PU
 - * Male Pin: Copper Alloy, Gold Plated
 - * Wire Harness: UL1007, 24AWG, 3Pcs
 - * Cable: Black, UL2464 22AWG*3C+Talc
PVC Jacket(UV Resistant), OD=5.0mm
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

4	Black	黑	4
3	Blue	藍	3
1	Brown	棕	1
Conn.1	Wire Color		Conn.2
Pin Out			

UNIT:mm
TOLERANCE
±0.5mm

TITLE M12 Conn T Cable Screw MF Conn MF Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. D	WC-REV. A.1	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO PS-030300-MF0-TSAXX	DRAWN BY Ruru	DATE 2017-02-22
CUSTOMER ALTW	CHECKED BY Rita	DATE 2017-02-22
	APPROVED BY Max	DATE 2017-02-22

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PS-030300-MF0-TSA10](#) [PS-030300-MF0-TSA05](#) [PS-030300-MF0-TSA02](#) [PS-030300-MF0-TSA01](#)