




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-880358~361	2008/03/08	Li Chi Cheng	Add the partition
C	LE314C0298~301	2014/12/06	Feng_Li	Change the Pin Out
D	LEN1730045~048	2017/02/24	Ruru	Change Outer Mold Design



Conn.1&2
Pin Assignments
Front View

4	Black	黑	4
3	Blue	藍	3
1	Brown	棕	1
Conn.1	Wire Color		Conn.2
Pin Out			

PS-030300-MM0-TSAXX

XX: 01~99Meters
01: 01Meter
02: 02Meters

99: 99Meters
Cable Length(L): 01~99meters

Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP68
一米水深, 24H
- * Housing: Black, PU
- * Male Pin: Copper Alloy, Gold Plated
- * Wire Harness: UL1007, 24AWG, 3Pcs
- * Cable: Black, UL2464 22AWG*3C+Talc
PVC Jacket(UV Resistant), OD=5.0mm
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm	
TOLERANCE	±0.5mm

TITLE M12 Conn T Cable Screw MM Conn MM Pin			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. D	WC-REV. A.3	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2017-02-24
DWG NO PS-030300-MM0-TSAXX	CHECKED BY Rita	DATE 2017-02-24
CUSTOMER ALTW	APPROVED BY Max	DATE 2017-02-24

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PS-030300-MM0-TSA05](#) [PS-030300-MM0-TSA10](#) [PS-030300-MM0-TSA01](#) [PS-030300-MM0-TSA02](#)