



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-880271~274	2008/03/31	Gao Ling	Add Cross
C	LEN1720142~145	2017/02/09	Ruru	Change Logo & Outer Mold Design & Note



Conn.1&2
Pin Assignments
Front View

4	Black	黑	4
3	Blue	藍	3
2	White	白	2
1	Brown	棕	1
Conn.1	Wire Color		Conn.2

PS-040400-FF0-TSAXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters

Cable Length(L):01~99Meters

- Note:
- * @D Important Dimension.
 - * Waterproof Rate: IP68
 - * Housing: Black, PU
 - * Male Pin: Copper Alloy, Gold Plated
 - * Wire Harness: UL1007, 24AWG, 4Pcs.
 - * Cable: Black, UL2464 22AWG*4C+Talc PVC Jacket (UV Resistant), OD=5.0mm
 - * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm		TITLE	M12 Conn T Cable Screw FF Conn FF Pin	Amphenol LTW	ITEM NO	DRAWN BY	Ruru	DATE	2017/02/09
TOLERANCE	±0.5 mm	SCALE	Free	SHEET	1 OF 1	DWG NO	PS-040400-FF0-TSAXX	CHECKED BY	Rita
REV.	C	SIZE	A4	@C	Inspection Item	CUSTOMER	ALTW	APPROVED BY	Max
1	2	3	4	5	6	7	8	FMW10702-01-01A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PS-040400-FF0-TSA02](#) [PS-040400-FF0-TSA05](#) [PS-040400-FF0-TSA01](#) [PS-040400-FF0-TSA10](#)