




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-880168~171	2008/03/11	Zhang Jin	Add Cross
C	LEN1720146~149	2017/02/10	Ruru	Change Logo & Outer Mold Design & Note

△



4	Black	黑	4
3	Blue	藍	3
2	White	白	2
1	Brown	棕	1
Conn.1	Wire Color	Conn.2	Pin Out

PS-040400-MF0-TSAXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters

Cable Length(L):01~99Meters

Note:

- * @C Important Dimension.
- * Waterproof Rate: IP68
- * Housing: Black, PU
- * Male Pin: Copper Alloy, Gold Plated
- * Wire Harness: UL1007, 24AWG, 4Pcs.
- * Cable: Black, UL2464 22AWG*4C+Talc PVC Jacket (UV Resistant), OD=5.0mm
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm	
TOLERANCE	±0.5 mm

TITLE M12 Conn T Cable Screw MF Conn MF Pin	
SCALE Free	SHEET 1 OF 1
REV. C	SIZE A4
@C :Inspection Item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	
DWG NO	PS-040400-MF0-TSAXX
CUSTOMER	ALTW

DRAWN BY Ruru	DATE 2017/02/10
CHECKED BY Rita	DATE 2017/02/10
APPROVED BY Max	DATE 2017/02/10

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PS-040400-MF0-TSA02](#) [PS-040400-MF0-TSA01](#) [PS-040400-MF0-TSA05](#) [PS-040400-MF0-TSA10](#)