




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1720166~169	2017/02/10	Ruru	Change Logo & Outer Mold Design & Note

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



8	Gray	灰	8
7	Purple	紫	7
6	Blue	藍	6
5	Green	綠	5
4	Yellow	黃	4
3	Orange	橘	3
2	Red	紅	2
1	Brown	棕	1
Conn.1	Wire Color		Conn.2

PS-080800-FF0-TSAXX

XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters

Cable Length(L):01~99Meters

- Note:
- * @C Important Dimension.
 - * Waterproof Rate: IP68
 - * Housing: Black, PU
 - * Male Pin: Copper Alloy, Gold Plated
 - * Wire Harness: UL1007, 24AWG, 8Pcs.
 - * Cable: Black, UL2464 24AWG*8C+Talc PVC Jacket (UV Resistant), OD=5.5mm
 - * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm				TITLE M12 Conn T Cable Screw FF Conn FF Pin				Amphenol LTW 安費諾亮泰企業股份有限公司				ITEM NO				DRAWN BY Ruru				DATE 2017/02/10											
TOLERANCE ±0.5 mm												SCALE Free		SHEET 1 OF 1		DWG NO PS-080800-FF0-TSAXX				CHECKED BY Rita				DATE 2017/02/10							
												REV. B		SIZE A4		QC :Inspection Item		CUSTOMER ALTW				APPROVED BY Max				DATE 2017/02/10					
1				2				3				4				5				6				7				8 FMW0702-01-01A			

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[PS-080800-FF0-TSA02](#) [PS-080800-FF0-TSA01](#) [PS-080800-FF0-TSA05](#) [PS-080800-FF0-TSA10](#)