


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


5	6	7	8
REV.	ECN NO.	DATE	SIGN
A		2019/04/10	Bovan Lu

DESCRIPTION
Initial Released.

Male Connector Position & Key Direction



Female Connector Position & Key Direction



※ This drawing is common drawing of series products.
The figure only shows individual position and key direction of male/female connectors.
Specific state of C1,2,3 connectors depends on part number. (see sheet 2/3)

ALTW
CONFIDENTIAL
2019-04-10
R&D DEPT.

- Note:
- * IP: IP68 (IM/24Hr.)
 - * Connector: Thermoplastic
 - * Pin: Copper Alloy
 - * Nut: Metal
 - * Other:

UNIT:mm		TOLERANCE ±0.5mm		TITLE M12, A-Code, T-Adaptor		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Bovan Lu		DATE 2019-04-10	
SCALE 1:1		SIZE A4		SHEET 1 OF 3		DWG NO TA-XXXX-XXXX-XXXX-XX		CHECKED BY Neo Tsai		DATE 2019-04-10		DATE 2019-04-10	
REV. A		WC-REV. A.17		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Max Yang		DATE 2019-04-10		DATE 2019-04-10	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

TA-XXXX-XXXX-XXXX-XX

-01: All connectors have the same number of pins.

C1 Connector Type

03: 3 pin
04: 4 pin
:
12: 12 pin

C1 Gender

M: Male Connector, Male Pin
F: Female Connector, Female Pin

C2 Connector Type

03: 3 pin
04: 4 pin
:
12: 12 pin

C2 Gender

M: Male Connector, Male Pin
F: Female Connector, Female Pin















C3 Connector Type

03: 3 pin
04: 4 pin
:
12: 12 pin


C3 Gender

M: Male Connector, Male Pin
F: Female Connector, Female Pin

UNIT:mm				TITLE MI2, A-Code, T-Adaptor				Amphenol LTW 安費諾亮泰企業股份有限公司				ITEM NO		DRAWN BY Bovan Lu		DATE 2019-04-10			
TOLERANCE —												SCALE 1:1		SIZE A4		SHEET 2 OF 3		DWG NO TA-XXXX-XXXX-XXXX-XX	
				REV. A		WC-REV. A.17						QC: Inspection item				CUSTOMER ALTW		APPROVED BY Max Yang	
1		2		3		4						5		6		7		8	

	A - code						
	3 Pin	4 Pin	5 Pin	6 Pin	8 Pin	10 Pin	12 Pin
Male							
Female							
	Pin# Color	Pin# Color	Pin# Color	Pin# Color	Pin# Color	Pin# Color	Pin# Color
Pin Out	Pin1 Black Pin3 White Pin4 Blue	Pin1 Black Pin2 White Pin3 Blue Pin4 Green	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin5 Red	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin6 Red Pin7 Gray	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin5 Red Pin6 Gray Pin7 Yellow Pin8 Orange	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin5 Red Pin6 Gray Pin7 Yellow Pin8 Orange Pin9 Brown Pin10 Purple	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin5 Red Pin6 Gray Pin7 Yellow Pin8 Orange Pin9 Brown Pin10 Purple Pin11 White/Red Pin12 Pink

Pin Assignments Front View



UNIT:mm TOLERANCE	 	TITLE M12, A-Code, T-Adaptor			ITEM NO		DRAWN BY Bovan Lu		DATE 2019-04-10
		SCALE 1:1	SIZE A4	SHEET 3 OF 3	DWG NO TA-AXXX-AXXX-AXXX-XX		CHECKED BY Neo Tsai		DATE 2019-04-10
		REV. A	WC-REV. A.17	QC: Inspection item	CUSTOMER ALTW		APPROVED BY Max Yang		DATE 2019-04-10

Amphenol LTW
安費諾亮泰企業股份有限公司

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[TA-A08M-A08F-A08M-01](#) [TA-A08F-A08F-A08F-01](#) [TA-A10M-A10M-A10F-01](#) [TA-A05F-A05M-A05M-01](#) [TA-A10M-A10F-A10F-01](#) [TA-A06F-A06M-A06M-01](#) [TA-A03F-A03F-A03F-01](#) [TA-A05F-A05M-A05F-01](#) [TA-A10F-A10F-A10F-01](#) [TA-A10M-A10M-A10M-01](#) [TA-A03F-A03M-A03F-01](#) [TA-A05F-A05F-A05F-01](#) [TA-A06M-A06M-A06M-01](#) [TA-A05M-A05M-A05M-01](#) [TA-A12M-A12F-A12F-01](#) [TA-A04M-A04M-A04M-01](#) [TA-A10F-A10M-A10M-01](#) [TA-A03M-A03M-A03F-01](#) [TA-A08F-A08M-A08M-01](#) [TA-A03M-A03F-A03F-01](#) [TA-A06F-A06F-A06F-01](#) [TA-A03M-A03M-A03M-01](#) [TA-A08M-A08F-A08F-01](#) [TA-A06F-A06M-A06F-01](#) [TA-A10F-A10M-A10F-01](#) [TA-A08M-A08M-A08M-01](#) [TA-A05M-A05M-A05F-01](#) [TA-A12F-A12F-A12F-01](#) [TA-A03F-A03M-A03M-01](#) [TA-A12M-A12M-A12F-01](#) [TA-A06M-A06F-A06F-01](#) [TA-A06M-A06M-A06F-01](#) [TA-A12M-A12M-A12M-01](#) [TA-A12F-A12M-A12M-01](#) [TA-A05M-A05F-A05F-01](#)