



SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



ET xx 0 1 x 2 xxxx G

No. OF POLES
02: 2 POLES

16: 16 POLES


COLOR

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange (RAL2011/P)
- 4 Yellow (RAL1018/A)
- 5 Green (RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey (RAL7035/D)
- 9 White (RAL1102)
- C Green (RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.



Material:

- Item ① Terminal(housing): Thermoplastic (UL94V-0)
- Item ② Terminal(cover): Thermoplastic (UL94V-0)
- Item ③ Clamp: Brass Ni plated
- Item ④ Female contact: Copper, Tin plated
- Item ⑤ Wire guard: Stainless steel
- Item ⑥ Terminal Screw: Steel, zinc plating "-" slot type
- Item ⑦ Flange Screw: Steel Zinc plating M3"/- slot type

- Electrical:
- | | | |
|--------------------------|-----------------|----------------------|
| | cULus | TUV |
| ● Voltage rating: | 300 V | 800V |
| ● Current rating: | 32 A | 32A |
| ● Wire range: | | 0.2-6mm ² |
| ● Solid wire(AWG): | 8-24 | |
| ● Stranded wire(AWG): | 8-24 | |
| ● Torque: | 7 LB-In | 0.8N.m |
| ● Screw: | M3.5 | |
| ● Wire strip length: | 10-11 mm | |
| ● Withstanding Voltage: | 1.6KV | 6KV |
| ● Operating temperature: | -40°C to +115°C | |
| ● Safety Approval: | cULus | TUV |
| ● Critical dimension: | ▽ | |



DIM		TOL			
		2P-4P	5P-8P	9P-12P	13P-16P
Dim L	N×7.62	±0.15	±0.20	±0.30	±0.40
Dim P	(N-1)×7.62	±0.15	±0.20	±0.30	±0.40
Dim C	(N+2)×7.62	±0.15	±0.20	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR, PROPERTY OF ANYTEK TECHNOLOGY CO., LTD.

TITLE	ET-7.62 W/Flange Series "-" (Match VC series)				
PART NO.	ETxx01x2xxxxG			DWG NO.	8ET0008
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Chen Bo 11/08/13	Chen Bo 11/08/13		
SHEET: 01/01				UNIT: mm	Tolerance
				SCALE: NONE	X. ±0.50
				REV.: B	X.X ±0.30
					X.XX ±0.10
					X° ±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[20020517-M041B01LF](#) [20020517-M031B01LF](#) [ET0301020000G](#) [ET0501520000G](#) [ET0601520000G](#)
[ET0701520000G](#) [ET0801520000G](#) [ET0901520000G](#) [ET1001520000G](#) [ET1101520000G](#) [ET1201520000G](#)
[ET1301520000G](#) [ET1401520000G](#) [ET1501520000G](#) [ET1601520000G](#) [ET03015200J0G](#) [ET04015200J0G](#)
[ET040152000AG](#)