



14.8 ±0.1

Ø15.6 ±0.1

Recommended Panel Cut-Out

23.5(REF)

Ø18.4

4.4

1.8

Ø6.6/C

14.5

Ø20.3

20.6

5/8"-27UNS

Connector 1

With Liquid Glue

Ø15.45 -0.25

Nut 3

2 Gasket

Note: E

\* Ø Important Dimension To Check.

\* Waterproof Rate: IP67, Unmated

\* Housing: Thermoplastic, Black

\* Pin: Copper Alloy, Gold Plated

\* Nut: Thermoplastic, Black

\* Gasket: Rubber, Black

B\* Use with waterproof cap or dust cap

Panel Thickness Max: 3.0mm

B\* Use without waterproof cap or dust cap

Panel Thickness Max: 4.5mm

\* Gasket and Nut are packed separately

in PE bags.

UNIT:mm



TOLERANCE

.X ±0.25

.XX ±0.1

.XXX ±0.05

ANGLES ±1°

TITLE

Standard  
Panel Lock 2Pin M Conn. M Pin

SCALE

1:1

SIZE

A4

SHEET

1

OF

1

REV.

E

WC-REV.

A.4

QC

Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

BB-02PMMS-LC7001

DWG NO

BB-02PMMS-LC7001

CUSTOMER

ALTW

DRAWN BY

Ruru

CHECKED BY

Rita

APPROVED BY

Max

DATE

2019-02-19

DATE

2019-02-19

DATE

2019-02-19

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1BB-02PMMS-LC7001](#)