


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN15C0204~207	2015/12/09	Vicky	Update Logo & Note




BB-03BFMM-LL7000
Color:Black



BB-03BFMM-LL7AXX

XX :01~99Meters
01 :01Meter
02 :02Meters
:
99 :99Meters

Cable Length(L):01~99Meters



- Note:
- * (QC) Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Lock Nut: Nylon+GF, Black
 - * Cable: Black, UL2464 20AWG*3C+Al/My, PVC Jacket, UV Resistant, OD=5.0mm
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

3	Yellow	黃
2	White	白
1	Black	黑
Conn.	Wire Color	
	Pin Out	

UNIT:mm				TITLE Standard Cable Lock 3Pin F Conn M Pin SCALE3:2 SIZEA4 SHEET1 OF 1 REV.B WC-REV.A.1 QC:Inspection item Amphenol LTW 安費諾亮泰企業股份有限公司				ITEM NO		DRAWN BY		DATE			
TOLERANCE		±0.5 mm						DWG NO		CHECKED BY		DATE			
								BB-03BFMM-LL7AXX		Rita		2015-12-09			
								CUSTOMER		APPROVED BY		DATE			
				ALTW		Lisa		2015-12-09							
1		2		3		4		5		6		7		8 FMM10702-01-02A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BB-03BFMM-LL7A05](#) [BB-03BFMM-LL7A01](#) [BB-03BFMM-LL7A02](#) [BB-03BFMM-LL7A10](#) [1BB-03BFMM-LL7A01](#)