





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1590409~13	2015/09/10	Ruru	Change Logo & Note

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

F
E
D
C
B
A



- Note:
- * @C Important Dimension.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 20#*3C+Al/My, UV Resistant, OD=5.0mm, Black
 - * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

Pin Assignments
Front View 前視圖

Yellow	黃	3
White	白	2
Black	黑	1
Wire Color	Conn.	
Pin Out		

UNIT:mm		TITLE
TOLERANCE		Standard,Cable Lock 3Pin M Conn M Pin
±0.5 mm		SCALE 1:1 SHEET 1 OF 1
	REV. B	SIZE A4 @C :Inspection Item

Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO	DRAWN BY Ruru	DATE 2015/09/10
		DWG NO BB-03BMMM-LL7AXX	CHECKED BY Rita	DATE 2015/09/10
		CUSTOMER ALTW	APPROVED BY Lion	DATE 2015/09/10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BB-03BMMM-LL7A01](#) [BB-03BMMM-LL7A05](#) [BB-03BMMM-LL7A10](#) [BB-03BMMM-LL7A02](#)