





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3I680I99	2016-07-19	Tom Gu	Change Part No. of Half Finished



Pin Assignments
Front View



4	Red	紅
3	Green	綠
2	White	白
1	Black	黑
Conn.	Wire Color	
	Pin Out	

BB-04AFFM-QL8E XX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
:
99 : 99Meters

Note:

- * (XX) Important Dimension To Check.
- * Waterproof Rate: IP68(Mated)
(in 1 meter water within 24 hours)
- * Working Voltage Rating: AC 300 V
- * Working Current Rating: 10A
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Rubber: Silicon, Gray
- * Cable: SJTW 16AWG*4C PVC Jacket
UV Resistant, OD=9.3, Black.
- * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm TOLERANCE ±0.5	TITLE X-Lok B-Size (Power) Molding F Conn F 4 Pin			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO	DRAWN BY Tom Gu	DATE 2016-07-19
	SCALE 3:2	SIZE A4	SHEET 1 OF 1			DWG NO BB-04AFFM-QL8EXX	CHECKED BY Spring Liu	DATE 2016-07-19
REV. B	WC-REV. A.1	QC: Inspection item			CUSTOMER ALTW	APPROVED BY Kevin Hu	DATE 2016-07-19	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BB-04AFFM-QL8E01](#)