

1	2	3	4	5	6	7	8	
				REV.	ECN NO.	DATE	SIGN	DESCRIPTION
				C	LEN-8C0102~105	2008/11/07	Ivan	Change to pin hole
				D	LEN1610418~421	2016/01/21	Ruru	Change Logo & Note
				E	LEN1650323/411~13	2016/05/10	Ruru	Modify Logo Position

6	Gray	灰	(24AWG)
5	Blue	藍	(20AWG)
4	Yellow	黃	(24AWG)
3	Green	綠	(24AWG)
2	Brown	棕	(20AWG)
1	White	白	(24AWG)
Conn.	Wire Color		
Pin Out			

Pin Assignments
Front View

Recommended Panel Cut-Out

UNIT:mm

TOLERANCE

±0.5

SCALE Free

SHEET 1 OF 1

REV. E

SIZE A4

QC :Inspection Item

Standard,Cable Lock 6Pin M Conn. F Pin

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO BBD-06PMFM-LL7AXX

CUSTOMER ALTW

DRAWN BY Ruru

CHECKED BY Rita

APPROVED BY Lisa

DATE 2016/05/10

DATE 2016/05/10

DATE 2016/05/10

AltW DCC. DEPT. CONFIDENTIAL 2016.05.18 ISSUED

AltW CONFIDENTIAL 2016.05.10 R&D DEPT.

Note:

- * @C Important Dimensions To Check.
- * Waterproof Rate: IP67
- * Housing: Black,Nylon+GF
- * Female Pin: Copper Alloy,Gold Plated
- * Nut: Black,Nylon+GF
- * Gasket: Black,EPDM
- * Cable: UL2464 (20AWG*2C+24AWG*4C)+Drain+AL/My Black,UV Resistant,OD=6.0mm
- * Use with waterproof cap or dust cap Panel Thickness Max: 2.5mm
- * Use without waterproof cap or dust cap Panel Thickness Max: 3.5mm
- * Cable Length Tolerance: 01M: ±40mm 02M~05M: ±60mm 06M~10M: ±100mm 11M~30M: ±200mm 31M~99M: ±500mm

1	2	3	4	5	6	7	8	
				REV.	ECN NO.	DATE	SIGN	DESCRIPTION
				C	LEN-8C0102~105	2008/11/07	Ivan	Change to pin hole
				D	LEN1610418~421	2016/01/21	Ruru	Change Logo & Note
				E	LEN1650323/411~13	2016/05/10	Ruru	Modify Logo Position

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BBD-06PMFM-LL7A10](#) [BBD-06PMFM-LL7A02](#) [BBD-06PMFM-LL7A05](#) [BBD-06PMFM-LL7A01](#)