




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0483-486	2008/09/10	Shin	Add Note
C	LEN15A0161-164	2015/09/23	Vicky	Update Logo & Note
D	LEN17A0004-007	2017/09/27	Ruru	Update View



2	Red	紅
1	Black	黑
Conn.	Wire Color	
	Pin Out	

Note:

- * ϕ Important Dimensions To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24#*2C+D+Al/My,UV, PVC Jacket, Black, OD=4.2mm
- * $\triangle B$ Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- * $\triangle B$ Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- * $\triangle C$ Cable Length Tolerance: 1M:±40mm
2M~5M:±60mm
6M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm	
TOLERANCE	±0.5 mm

TITLE Standard Cable Screw 2Pin M Conn M Pin			
SCALE 3:2	SIZE A4	SHEET 1	OF 1
REV. D	WC-REV. A.1	ϕ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DWG NO	CUSTOMER	DRAWN BY	CHECKED BY	APPROVED BY	DATE
	BD-02PMMM-SL7AXX	ALTW	Ruru	Rita	Max	2017-09-27
						2017-09-27
						2017-09-27

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-02PMMM-SL7A01](#) [BD-02PMMM-SL7A10](#) [BD-02PMMM-SL7A05](#) [BD-02PMMM-SL7A02](#)