



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0489-492	2008/09/19	Shin	Add Note
C	LEN15A0171-174	2015/09/25	Vicky	Update Logo & Note
D	LEN17A0008-011	2017/09/27	Ruru	Update View



BD-03PMMM-SL7AXX



XX: 01~99Meter

01: 01Meter

02: 02Meters

99: 99Meters

Cable Length(L): 01~99Meters

Pin Assignments
Front View

Recommended Panel Cut-Out

3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

Note:

- * $\varnothing$ Important Dimensions To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24#*3C+D+Al/My,UV, PVC Jacket, Black, OD=4.5mm
- * $\triangle A$ Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- * $\triangle B$ Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- * $\triangle C$ Cable Length Tolerance: 1M: ± 40 mm
2M~5M: ± 60 mm
6M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm

UNIT:mm	
TOLERANCE	± 0.5 mm

TITLE Standard Cable Screw 3Pin M Conn M Pin			
SCALE 3:2	SIZE A4	SHEET 1	OF 1
REV. D	WC-REV. A.1	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2017-09-27
DWG NO BD-03PMMM-SL7AXX	CHECKED BY Rita	DATE 2017-09-27
CUSTOMER ALTW	APPROVED BY Max	DATE 2017-09-27

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-03PMMM-SL7A05](#) [BD-03PMMM-SL7A01](#) [BD-03PMMM-SL7A02](#) [BD-03PMMM-SL7A10](#)