




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1540247~53	2014/12/23	Jinhai	Change Logo





Conn



BD-04BFFM-LL7AXX

XX :01~99Meters
01 :01Meter
02 :02Meters
...
99 :99Meters

Cable Length(L):01~99Meters



Pin Assignments
Front View

4	Yellow	黃
3	Red	紅
2	Green	綠
1	White	白
Conn.	Wire Color	
Pin Out		

Note:

- * CC Important Dimension To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Lock Nut: Nylon+GF, Black
- * O-Ring: EPDM, Black
- * Cable: UL2464 24AWG*4C+D+AL/My
- * PVC Jacket UV Resistant, OD=5.8, Black
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

UNIT:mm				TITLE Standard, Cable Lock 4Pin F Conn F Pin			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Jinhai		DATE 2014-12-23		
TOLERANCE ±0.5mm									SCALE 1:1		SIZE A4		DWG NO BD-04BFFM-LL7AXX		CHECKED BY Tom
				REV. B		WC-REV. A.1		SHEET 1 OF 1		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2014-12-23	
						QC:Inspection item									

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-04BFFM-LL7A01](#) [BD-04BFFM-LL7A10](#) [BD-04BFFM-LL7A02](#) [BD-04BFFM-LL7A05](#) [1BD-04BFFM-LL7A01](#)