

1	2	3	4	5	6	7	8	
				REV. B	ECN NO. LEN15C0320~325	DATE 2015/12/15	SIGN Vicky	DESCRIPTION Update Logo & Note

Altwatermark: ALTW

ALTW
CONFIDENTIAL
2015.12.15
R&D DEPT.

BD-04BFFM-SL7000
Color:Black

ALTW
DCC. DEPT.
CONFIDENTIAL
2015.12.18
ISSUED

BD-04BFFM-SL7AXX
XX:01~99Meter
01:01Meter
02:02Meters
:
:
99:99Meters
Cable Length(L):01~99Meters

Pin Assignments
Front View

4	Yellow	黃
3	Red	紅
2	Green	綠
1	White	白
Conn.	Wire Color	
Pin Out		

Note:

- * @Important Dimension To Check.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24AWG*4C+D+Al/My, PVC Jacket, UV Resistant, OD=5.8mm, Black
- * Cable Length Tolerance:01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm		TITLE Standard	
TOLERANCE		Cable Screw 4Pin F Conn F Pin	
±0.5 mm		SCALE Free	SHEET 1 OF 1
		REV. B	SIZE A4
		QC :Inspection Item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO
DWG NO BD-04BFFM-SL7AXX
CUSTOMER ALTW

DRAWN BY Vicky
CHECKED BY Rita
APPROVED BY Lion

DATE 2015/12/15
DATE 2015/12/15
DATE 2015/12/15

1

2

3

4

5

6

7

8 FMW10702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-04BFFM-SL7A02](#) [1BD-04BFFM-SL7A01](#) [BD-04BFFM-SL7A10](#) [BD-04BFFM-SL7A01](#) [BD-04BFFM-SL7A05](#)