




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0495-498	2008/09/19	Shin	Add Note
C	LEN15A0181-184	2015/09/25	Vicky	Update Logo & Note
D	LEN17A0012-015	2017/09/27	Ruru	Update View




XX:01~99Meter
01:01Meter
02:02Meters
:
99:99Meters
Cable Length(L):01~99Meters

1 BD-04PMMM-SL7000
Color:Black



Pin Assignments
Front View



Recommended Panel Cut-Out

4	Yellow	黃
3	Red	紅
2	Green	綠
1	White	白
Conn.	Wire Color	
	Pin Out	

- Note:
- * $\varnothing$ Important Dimensions To Check
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL2464 24#*4C+D+Al/My,UV, PVC Jacket, Black, OD=5.8mm
 - * $\triangle A$ Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
 - * $\triangle B$ Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
 - * $\triangle C$ Cable Length Tolerance: 1M:±40mm
2M~5M:±60mm
6M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm	
TOLERANCE	±0.5 mm

TITLE Standard Cable Screw 4Pin M Conn M Pin			
SCALE 3:2	SIZE A4	SHEET 1 OF 1	
REV. D	WC-REV. A.1	$\varnothing$ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2017-09-27
DWG NO BD-04PMMM-SL7AXX	CHECKED BY Rita	DATE 2017-09-27
CUSTOMER ALTW	APPROVED BY Max	DATE 2017-09-27

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-04PMMM-SL7A02](#) [BD-04PMMM-SL7A01](#) [BD-04PMMM-SL7A10](#) [BD-04PMMM-SL7A05](#)