


Cable (2)

XX:01~99Meter
01:01Meter
02:02Meters


99:99Meters

Cable Length(L):01~99Meters



Pin Assignments

Front View



Recommended Panel Cut-Out

5	Green	綠
4	White	白
3	Black	黑
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	
	Pin Out	

Note:

- *  Important Dimensions To Check
- * Waterproof Rate: IP67
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Cable: UL2464 24#*5C+D+Al/My,UV, PVC Jacket, Black, OD=5.0mm
- *  Use with waterproof cap or dust cap
Panel Thickness Max: 2.5mm
- *  Use without waterproof cap or dust cap
Panel Thickness Max: 3.5mm
- *  Cable Length Tolerance: 1M:±40mm
2M~5M:±60mm
6M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT: mm	
TOLERANCE	
$\pm 0.5 \text{ mm}$	

TITLE	Standard
	Cable Lock 5Pin M Conn M Pin

SCALE 3:2	SIZE A4	SHEET 1 OF 1
REV. D	WC-REV. A.1	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BD-05PMMM-LL7A02](#) [BD-05PMMM-LL7A05](#) [BD-05PMMM-LL7A10](#) [BD-05PMMM-LL7A01](#)